


2NKX3A

 REV.
0


ALL DIMENSIONS ARE IN INCHES AND MILLIMETERS

UNITS	A	B	C	D -.06	E	2E ±.03	G	H +.05	J	K	K2	N
IN	6.50	6.00	12.84	3.50	2.75	5.50	.13	.34	1.00	.88	1.88	2.31
MM	165	152	326	89	70	140	3	9	25	22	48	59

UNITS	O	P ²	U -.0005	V MIN	W	AA	BA	BS	ES MIN	EV	SQ KEY
IN	6.72	6.44	.8750	2.06	.06	3/4 NPT	2.25	6.88	1.41	.50	.188
MM	171	164	22.225	52	2		57	175	36	13	4.78

FRAME	UNITS	2F ±.03
143T	IN	4.00
	MM	102
145T	IN	5.00
	MM	127

1. ALL ROUGH DIMENSIONS MAY VARY BY .25" DUE TO CASTING AND/OR FABRICATION VARIATIONS.
2. LARGEST MOTOR WIDTH.
3. TOLERANCES SHOWN ARE IN INCHES ONLY.

 DRAWING NO. PAGE 1 of 1
2NKX3A

 REV.
0