



PARTS LIST FOR
GC-5004-3MAH and GC-6004-3MGH
(GRAINGER ITEM #6CGP0 AND #6CGP1)
COLD WATER PRESSURE WASHER
(AFTER SERIAL #10738662)

MANUFACTURED FOR W.W. GRAINGER INC.
FOR REPLACEMENT PARTS CALL GRAINGER PARTS 800-323-0620

ENGINE OIL GRADE:	SAE10W-30 (Grainger Item #4F743)
ENGINE OIL CAPACITY:	64 oz.
PUMP OIL GRADE:	SAE30W Non-Detergent (Grainger Item #4ZF21)
PUMP OIL CAPACITY:	
GC-6004-3MGH:	40.6 oz.
GC-5004-3MAH:	32.0 oz.
PRESSURE NOZZLE SIZE	
GC-6004-3MGH:	3.0
GC-5004-3MAH:	3.5

This Parts Listing has been compiled for your benefit. You can be assured your Cold Water Pressure Washer was constructed and designed with quality and performance in mind. Each component has been rigorously tested to insure the highest level of acceptance.

The contents of this Parts Listing are based on the latest product information available at the time of publication. Manufacturer reserves the right to make changes in price, color, materials, equipment, specifications or models at any time without notice.

WARNING

THIS IS A PROFESSIONAL HIGH PRESSURE, COLD WATER PRESSURE WASHER. CAUTION SHOULD BE OBSERVED WHEN USING OR REPAIRING THIS UNIT! READ AND FOLLOW THE SAFETY WARNINGS LISTED BELOW BEFORE ATTEMPTING ANY REPAIRS ON THIS PRESSURE WASHER!

SAFETY WARNINGS

- 1. NEVER alter or modify the equipment. Be sure any accessory items and system components being used will withstand the pressure developed. Use only genuine manufacturer parts for repair of your pressure washer. Failure to do so can cause hazardous operating conditions and will VOID warranty.
- 2. NEVER make adjustments on machinery while the unit is connected to the power source. Turning over the machinery by hand during adjustment or cleaning might start the machinery, causing serious injury to the operator.
- 3. Know how to stop and bleed pressures quickly. Be thoroughly familiar with controls.
- 4. Before servicing the unit, turn unit off, relieve the water pressure and allow the unit to cool down. Do not make repairs while the unit is running. Service in a clean, dry, flat area.
- 5. After testing the machine, DO NOT leave the pressurized unit unattended. Shut off the unit and release trapped pressure before leaving.

Table of Contents

NOTES3

SPECIFICATIONS.....5

FRAME ASSEMBLY FOR GC-5004-3MAH (AFTER SERIAL #10738662)6

FRAME ASSEMBLY FOR GC-6004-3MGH (AFTER SERIAL #10738662).....8

CWC PLUMBING ASSEMBLY 5004 AND 5005.....10

CWC PLUMBING ASSEMBLY 600412

PUMP ASSEMBLY (3-0213)14

PUMP ASSEMBLY (3-0261)16

UNLOADER ASSEMBLY (8-0522)18

HONDA ENGINE ASSEMBLY (851-0385).....20

NOTES

SERIAL # BREAK

10552631
10738662

DATE

12-16-10
09-26-13

REASON

PAINT CODE CHANGE FROM A42 TO A01. FRAMES CHANGED FROM GRAY TO BLACK.
NEW FUEL TANK


NOTES

SPECIFICATIONS

MODEL NUMBER	GC-5004-3MAH	GC-6004-3MGH
Operating Pressure (PSI/Bar):	5000/344.7	6000/413.7
High Pressure Nozzle:	3.5	3.0
Water Volume (GPM/lpm):	4.0/15.1	3.7/14.0
Engine:	Honda	Honda
Model #	GX630	GX630
Engine Type	4 Stroke, Overhead Valve, Single Cylinder	4 Stroke, Overhead Valve, Single Cylinder
Oil Type	SAE10W-30 (Grainger Item #4F743)	SAE10W-30 (Grainger Item #4F743)
Oil Capacity (oz./liter)	64/1.9	64/1.9
Low Oil Protection	Oil Alert™	Oil Alert™
Fuel Type	Unleaded Gasoline 86 Octane Minimum	Unleaded Gasoline 86 Octane Minimum
Fuel Capacity (gal./liter)	13.0/49.1	13.0/49.1
Starting	Electric	Electric
Maximum No Load RPM	3600 (+/- 100) RPM	3600 (+/- 100) RPM
Thermal Relief Valve	Relieves heated water during unloader bypass stage	Relieves heated water during unloader bypass stage
Pump:	Belt Driven, Oil Bath, Triplex Piston	Belt Driven, Oil Bath, Triplex Piston
Oil Type	SAE30W Non-Detergent (Grainger Item #4ZF21)	SAE30W Non-Detergent (Grainger Item #4ZF21)
Oil Capacity (oz./liters)	32/0.95	40.6/1.20
Plungers	Ceramic	Ceramic
Manifold	Forged Brass	Forged Brass
Valves	Stainless Steel	Stainless Steel
Unloader	Preset	Preset
Unit Net Weight (lbs/Kg)	378/171.5	378/171.5
Unit Shipping Weight (lbs/Kg)	521/247	521/247
Unit Net Dimension (in/cm)	43Lx27.75Wx36H/109Lx70.5Wx91.5H	43Lx27.75Wx36H/109Lx70.5Wx91.5H
Unit Shipping Dimension (in/cm)	46.5Lx31.5Wx48.5H/118Lx80Wx123H	46.5Lx31.5Wx48.5H/118Lx80Wx123H

FRAME ASSEMBLY FOR GC-5004-3MAH (AFTER SERIAL #10738662)


GC-5004-3MAH 051214 ALC



FRAME ASSEMBLY						GC-5004-3MAH 051214 ALC	
ITEM	DESCRIPTION	PART #	QTY	ITEM	DESCRIPTION	PART #	QTY
1	GROMMET	33-0002	4	56	BOLT	27-9550	1
2	FRAME	5-0136A01	1	57	DECAL - OPERATION (SEE 71-1028)	N/A	1
3	LOCKNUT	30-0157	9	58	ASSEMBLY - FUEL TANK (59-67)	851-0400	1
4	WASHER	28-0003	15	59	PLUG	24-0009	1
5	WHEEL	14-0127	4	60	DECAL - RISK OF BURNS (SEE 71-1028)	N/A	1
6	LOCKNUT	30-0117	4	61	FUEL TANK	12-0248A09	1
7	DECAL- MI-T-M EMISSIONS	N/A	1	62	FUEL GAUGE	12-0184	1
8	DECAL- SILVER STICKER	N/A	1	63	BARB	23-0051	1
9	EDGING *(ONE FOOT REQUIRED)	33-0020	1	64	FUEL PICK UP	33-0271	1
10	BOLT	27-0016	3	65	FUEL CAP CATCH	12-0228	1
11	WASHER	28-0021	10	66	ELBOW	23-0054	1
12	SUPPORT BRACKET	13-0120A01	1	67	FUEL CAP	12-0229	1
13	LOCKNUT	30-0155	9	68	TAG - WATER SUPPLY INLET (E)	34-0097	1
14	TAG	34-0096	1	69	CWC-PLUMBING ASSEMBLY 5004_5005	N/A	1
15	DECAL - RISK OF INJURY (SEE 71-1028)	N/A	1	70	PUMP	3-0213	1
16	BATTERY BOX	33-0092	1	71	BOLT	27-0067	4
17	BATTERY RETAINER	20-0264A01	1	72	ASSEMBLY - BELTGUARD BACK (73-76)	851-0310	1
18	BOLT	27-0066	4	73	DECAL - WARNING (SEE 71-1028)	N/A	1
19	CABLE	32-9112	1	74	BELTGUARD BACK	6-0083A01	1
20	CABLE	32-9111	1	75	DECAL - WARNING (SEE 71-1028)	N/A	1
21	ENGINE ASSY	851-0385	1	76	EDGING *(TWO FEET REQUIRED)	33-0020	1
22	BOLT	27-0121	4	77	SHEAVE	10-0118	1
23	WASHER	28-0023	11	78	BUSHING	9-0005	1
24	LOCKNUT	30-0159	6	79	SHEAVE	10-0037	1
25	CLAMP WORM	42-0004	3	80	BELT	11-0055	2
26	FUEL HOSE *(FOUR FEET REQUIRED)	15-0008	1	81	BUSHING	9-0017	1
27	DECAL - RISK OF BURNS (SEE 71-1028)	N/A	2	82	ASSEMBLY BELTGUARD COVER (27, 83-87)	851-0348	1
28	KEY	43-0078	1	83	EDGING *(FOUR FEET REQUIRED)	33-0020	1
29	AIR CLEANER ADAPTER	62-0229	1	84	BELTGUARD COVER	6-0064A01	1
30	FUEL HOSE *(THREE FEET REQUIRED)	15-0261	1	85	FASTENER	33-0197	1
31	ELBOW	23-0050	1	86	DECAL - NOZZLE (SEE 71-1028)	N/A	1
32	HOSE CLAMP	42-0011	1	87	GROMMET	33-0001	5
33	HOSE *(TWO FEET REQUIRED)	15-0305	1	88	NOZZLE	18-0392	1
34	HOSE BARB	23-0360	1	-	NOZZLE	18-0393	1
35	PLUG	23-0411	1	-	NOZZLE	18-0395	1
36	DRAIN HOSE	70-0555	1	-	NOZZLE	18-0396	1
37	LOCKWASHER	28-1028	2	89	DECAL - GRAINGER 800# LARGE (SEE 71-1028)	N/A	1
38	BOLT	27-0068	1	90	DECAL - MI-T-M STRIPE (SEE 71-1028)	N/A	1
39	CLIP	33-0291	2	91	DECAL - MI-T-M (SEE 71-1028)	N/A	1
40	BOLT	27-0015	12	92	ASSEMBLY GUN W/S.S. LANCE 48" (93-98)	851-0309	1
41	WASHER	28-0002	8	93	QUICK CONNECT	17-0005	1
42	CARB CANISTER STRAP	20-1187A01	2	94	GUN	16-0343	1
43	CARB CANISTER	62-0212	1	95	GRIP	7-0002	1
44	FUEL HOSE *(SIX FEET REQUIRED)	15-0008	1	96	WAND	16-0342A01	1
45	LOCKNUT	30-0161	4	97	DECAL - RISK OF INJECTION (SEE 71-1028)	N/A	1
46	WASHER	28-0030	8	98	QUICK CONNECT	17-0036	1
47	PUMP BRACKET	5-0101A01	1	99	O-RING	25-0122	1
48	LOCKWASHER	29-0055	4	100	O-RING	25-0123	1
49	BOLT	27-8471	4	101	PRESSURE HOSE ASSEMBLY (102-104)	851-0317	1
50	BOLT	27-0167	4	102	QC SOCKET	17-0041	1
51	BOLT	27-0118	2	103	HOSE	15-0178	1
52	BRACKET	13-0003A01	1	104	QUICK CONNECT	17-0006	1
53	BOLT	27-0576	1	105	BATTERY	32-0058	1
54	PUSH/PULL TOGGLE CLAMP	33-0400	1	-	DECAL SET - CWC SERIES - MITM	71-1028	1
55	NUT	30-0004	1	*MUST ORDER IN ONE FOOT LENGHTS			


FRAME ASSEMBLY FOR GC-6004-3MGH (AFTER SERIAL #10738662)

GC-6004-3MGH-051214 ALC



GC-6004-3MGH 051214 ALC							
FRAME ASSEMBLY							
ITEM	DESCRIPTION	PART #	QTY	ITEM	DESCRIPTION	PART #	QTY
1	GROMMET	33-0002	4	56	BOLT	27-9550	1
2	FRAME	5-0136A01	1	57	DECAL - OPERATION (SEE 71-1028)	N/A	1
3	WASHER	28-0003	15	58	ASSEMBLY - FUEL TANK (59-67)	851-0400	1
4	LOCKNUT	30-0157	9	59	PLUG	24-0009	1
5	WHEEL	14-0127	4	60	DECAL - RISK OF BURNS (SEE 71-1028)	N/A	1
6	LOCKNUT	30-0117	4	61	FUEL TANK	12-0248A09	1
7	DECAL- MI-T-M EMISSIONS	N/A	1	62	FUEL GAUGE	12-0184	1
8	DECAL- SILVER STICKER	N/A	1	63	BARB	23-0051	1
9	EDGING (ONE FOOT REQUIRED)	33-0020	1	64	FUEL PICK UP	33-0271	1
10	BOLT	27-0016	3	65	FUEL CAP CATCH	12-0228	1
11	WASHER	28-0021	10	66	ELBOW	23-0054	1
12	SUPPORT BRACKET	13-0120A01	1	67	FUEL CAP	12-0229	1
13	LOCKNUT	30-0155	9	68	TAG - WATER SUPPLY INLET (E)	34-0097	1
14	TAG	34-0096	1	69	CWC-PLUMBING ASSEMBLY 6004	N/A	1
15	DECAL - RISK OF INJURY (SEE 71-1028)	N/A	1	70	PUMP	3-0261	1
16	BATTERY BOX	33-0092	1	71	BOLT	27-0067	4
17	BATTERY RETAINER	20-0264A01	1	72	ASSEMBLY - BELTGUARD BACK (73-76)	851-0310	1
18	BOLT	27-0066	4	73	DECAL - WARNING (SEE 71-1028)	N/A	1
19	CABLE	32-9112	1	74	BELTGUARD BACK	6-0083A01	1
20	CABLE	32-9111	1	75	DECAL - WARNING (SEE 71-1028)	N/A	1
21	ENGINE ASSY	851-0385	1	76	EDGING *(TWO FEET REQUIRED)	33-0020	1
22	BOLT	27-0121	4	77	SHEAVE	10-0043	1
23	WASHER	28-0023	11	78	BUSHING	9-0005	1
24	LOCKNUT	30-0159	6	79	BOLT	27-0771	2
25	CLAMP WORM	42-0004	3	80	SHEAVE	10-0046	1
26	FUEL HOSE *(FOUR FEET REQUIRED)	15-0008	1	81	BELT	11-0068	2
27	DECAL - RISK OF BURNS (SEE 71-1028)	N/A	2	82	BUSHING	9-0017	1
28	KEY	43-0078	1	83	ASSEMBLY BELTGUARD COVER (27, 84-88)	851-0348	1
29	AIR CLEANER ADAPTER	62-0229	1	84	EDGING *(FOUR FEET REQUIRED)	33-0020	1
30	FUEL HOSE *(THREE FEET REQUIRED)	15-0261	1	85	BELTGUARD COVER	6-0064A01	1
31	ELBOW	23-0119	1	86	FASTENER	33-0197	1
32	HOSE CLAMP	42-0011	1	87	DECAL - NOZZLE (SEE 71-1028)	N/A	1
33	HOSE *(TWO FEET REQUIRED)	15-0305	1	88	GROMMET	33-0001	5
34	HOSE BARB	23-0360	1	89	NOZZLE	18-0387	1
35	PLUG	23-0411	1	-	NOZZLE	18-0388	1
36	DRAIN HOSE	70-0555	1	-	NOZZLE	18-0390	1
37	LOCKWASHER	28-1028	2	-	NOZZLE	18-0391	1
38	BOLT	27-0068	1	90	DECAL - GRAINGER 800# LARGE (SEE 71-1028)	N/A	1
39	CLIP	33-0291	2	91	DECAL - MI-T-M STRIPE (SEE 71-1028)	N/A	1
40	BOLT	27-0015	10	92	DECAL - MI-T-M (SEE 71-1028)	N/A	1
41	WASHER	28-0002	8	93	ASSEMBLY GUN W/S.S. LANCE 48" (94-99)	851-0361	1
42	CARB CANISTER STRAP	20-1187A01	2	94	QUICK CONNECT	17-0005	1
43	CARB CANISTER	62-0212	1	95	GUN	16-0447	1
44	FUEL HOSE *(SIX FEET REQUIRED)	15-0008	1	96	GRIP	7-0002	1
45	LOCKNUT	30-0161	4	97	WAND	16-0342A01	1
46	WASHER	28-0030	8	98	DECAL - RISK OF INJECTION (SEE 71-1028)	N/A	1
47	PUMP BRACKET	5-0101A01	1	99	QUICK CONNECT	17-0036	1
48	LOCKWASHER	29-0055	4	100	O-RING	25-0122	1
49	BOLT	27-8471	4	101	O-RING	25-0123	1
50	BOLT	27-0167	4	102	HIGH PRESSURE HOSE ASSEMBLY (103-105)	851-0362	1
51	BOLT	27-0118	2	103	QC SOCKET	17-0041	1
52	BRACKET	13-0003A01	1	104	HOSE	15-0255	1
53	BOLT	27-0576	1	105	QUICK CONNECT	17-0006	1
54	PUSH/PULL TOGGLE CLAMP	33-0400	1	106	BATTERY	32-0058	1
55	NUT	30-0004	1	-	DECAL SET - CWC	71-1028	1


CWC PLUMBING ASSEMBLY 5004_5005



CWC-PLUMBING ASSEMBLY 5004_5005 050814 ALC

CWC PLUMBING ASSEMBLY 5004_5005 050814 ALC			
CWC-PLUMBING ASSEMBLY 5004_5005			
ITEM	DESCRIPTION	PART #	QTY
1	ELBOW	24-0092	1
2	VALVE	22-0319	1
3	HEAT SHRINK TUBING *(ONE FOOT REQUIRED)	33-0272	1
4	UNLOADER	8-0522	1
5	NIPPLE	24-0010	1
6	BOLT	27-0074	2
7	MANIFOLD BLOCK	51-0020	1
8	WASHER	28-0003	2
9	LOCKNUT	30-0157	2
10	RELIEF VALVE	22-0005	1
11	TEE	23-0235	1
12	FILTER	19-0207	1
13	HOSE BARB	23-0120	1
14	HOSE CLAMP	42-0011	2
15	EASY START VALVE	22-0242	1
16	HOSE	15-0140	1
17	ELBOW	23-0324	1
18	TEE	23-0117	1
19	HOSE BARB	23-0105	1
20	HOSE *(THREE FEET REQUIRED)	15-0007	1
21	REDUCER BUSHING	23-0016	1
22	PLUG	39-0017	1
23	TEE	24-0026	1
24	NIPPLE	24-0002	1
25	HOSE	15-0254	1
26	QUICK CONNECT	17-0042	1
27	O-RING	25-0123	1
*MUST ORDER IN ONE FOOT LENGTHS			

CWC PLUMBING ASSEMBLY 6004




CWC-PLUMBING ASSEMBLY 6004 050814 ALC

CWC-PLUMBING ASSEMBLY 6004 050814 ALC			
CWC-PLUMBING ASSEMBLY 6004			
ITEM	DESCRIPTION	PART #	QTY
1	HOSE	15-0254	1
2	90° ELBOW FITTING	24-0074	1
3	UNLOADER	8-0373	1
4	REDUCER	24-0282	1
5	QUICK CONNECT	17-0042	1
6	HOSE *(TWO FEET REQUIRED)	15-0007	1
7	HOSE BARB	23-0418	1
8	HOSE CLAMP	42-0011	2
9	BARB	23-0045	1
10	BOLT	27-0074	2
11	MANIFOLD BLOCK	51-0034	1
12	PLUG	39-0016	1
13	LOCKNUT	30-0157	2
14	WASHER	28-0003	2
15	NIPPLE	24-0031	1
16	BURST DISC AND HOLDER	22-0217	1
17	FILTER	19-0207	1
18	TEE	23-0235	1
19	TEE	23-0124	1
20	NIPPLE	23-0247	1
21	HOSE	15-0140	1
22	EASY START VALVE	22-0242	1
23	RELIEF VALVE	22-0005	1
24	STREET TEE	23-0058	1
25	NIPPLE	24-0002	1
*MUST ORDER IN ONE FOOT LENGTHS			

PUMP ASSEMBLY (3-0213)

TORQUE SPECS.	
POSITION	FT-LBS
1	18
10	7.4
16	7.4
24	8.8
32	50
39	37




3-0213-061113-MLK

3-0213 061113 MLK							
PUMP ASSEMBLY							
ITEM	DESCRIPTION	Mi-T-M #	QTY	ITEM	DESCRIPTION	Mi-T-M #	QTY
1	BOLT	27-8884	8	28	OIL SIGHT GLASS	46-0926	1
2	COVER	46-0909	1	29	O-RING	25-0514	1
3	O-RING	25-0512	2	30	SHIM - .05mm	46-0947	1
4	OIL SEAL	26-0243	1	-	SHIM - .10mm	46-0948	0
5	BEARING	48-0073	2	-	SHIM - .19mm	46-0949	0
6	PUMP KEY	43-0091	1	-	SHIM - .25mm	46-0950	0
7	CRANKSHAFT	46-0944	1	31	COVER	46-0918	1
8	PLUG	39-0203	3	32	VALVE CAP	39-0201	6
9	O-RING	25-0510	4	33	BACK-UP RING	25-0509	6
10	BOLT	27-8888	6	34	O-RING	25-0386	6
11	COVER	46-0912	1	35	VALVE (SEE KIT 70-0314)	22-0318	6
12	O-RING	25-0513	1	36	BACK-UP RING (SEE KIT 70-0314)	25-0516	6
13	O-RING	25-0370	1	37	O-RING (SEE KIT 70-0314)	25-0407	6
14	OIL SIGHT GLASS	46-0670	1	38	PUMP MANIFOLD	46-0900	1
15	SPRING RETAINER	46-0671	1	39	BOLT	27-8470	8
16	BOLT	27-8892	6	40	O-RING	25-0372	1
17	LOCKWASHER	29-0153	14	41	PLUG	39-0202	1
18	CONNECTING ROD	46-0913	3	42	SUPPORT RING (SEE KIT 70-0317)	46-0901	3
19	PLUNGER ROD	46-0915	3	43	HIGH PRESSURE SEAL (SEE KIT 70-0317)	46-0902	3
20	PIN	46-0914	3	44	BACK-UP RING (SEE KIT 70-0317)	46-0903	3
21	WASHER	46-0916	3	45	GUIDE	46-1201	3
22	PISTON	46-0917	3	46	BACK-UP RING (SEE KIT 70-0317)	46-0905	3
23	WASHER	29-0014	3	47	LOW PRESSURE SEAL (SEE KIT 70-0317)	46-0906	3
24	BOLT	27-8965	3	48	O-RING (SEE KIT 70-0317)	25-0511	3
25	DIPSTICK	39-0204	1	49	GUIDE REAR	46-1200	3
26	RETAINER	46-0924	1	50	OIL SEAL	26-0242	3
27	PUMP	46-0925	1	51	CRANKCASE	46-0911	1

REPLACEMENT KITS				
Mi-T-M KIT #	DESCRIPTION	ITEMS	# OF ASSEMBLIES	# OF CYLINDERS
70-0317	KIT - WATER SEALS	42-44, 46-48	3	3
70-0314	KIT - VALVES	35, 36, 37	6	3

PUMP ASSEMBLY (3-0261)



TORQUE SPECS.	
POSITION	FT-LBS
1	95.9
12	33.2
18	29.5
27	14.8
36	14.8
37	7.4
42	14.8
49**	14.8
56	14.8
** USE LOC-TITE 542	

3-0261 061113-MLK

PUMP ASSEMBLY

ITEM	DESCRIPTION	Mi-T-M #	QTY	ITEM	DESCRIPTION	Mi-T-M #	QTY
1	VALVE PLUG	46-1203	3	29	CRANKCASE COVER OPEN	46-1217	1
2	RING	25-0592	3	30	O-RING	25-0590	2
3	O-RING	25-0139	6	31	BEARING	48-0085	2
4	CAP	46-1206	3	32	KEY	46-0602	1
5	VALVE ASSEMBLY (SEE KIT 70-0431)	SEE KIT	6	33	CRANKSHAFT	46-1210	1
6	GUIDE	46-1205	3	34	CONNECTING ROD PIN	43-0118	3
7	O-RING	25-0160	3	35	O-RING	25-0014	1
8	BACKUP RING	25-0430	3	36	PLUG	39-0017	1
9	SPACER	46-1204	3	37	BOLT	27-8812	4
10	O-RING	25-0130	3	38	SIGHT GLASS	46-1163	1
11	BACKUP RING	25-0591	3	39	O-RING	25-0059	1
12	BOLT	27-8073	8	40	CRANKCASE COVER	46-1212	1
13	LOCKWASHER	29-0155	8	41	O-RING	25-0339	1
14	MANIFOLD	46-1202	1	42	BOLT	27-8435	6
15	WASHER	28-1038	1	43	LOCKWASHER	29-1014	1
16	PLUG	39-0019	1	44	CONNECTING ROD	46-1211	3
17	WASHER	28-1002	1	45	PLUNGER ROD	46-1213	3
18	PLUG	39-0018	2	46	SLINGER WASHER	46-1214	3
19	HIGH PRESSURE SEAL ASSEMBLY (SEE KIT 70-0433 & 70-0434)	SEE KIT	3	47	PLUNGER	46-1215	3
20	HIGH PRESSURE INTERMEDIATE SEAL RETAINER (SEE KIT 70-0434)	SEE KIT	3	48	O-RING	25-0310	3
21	LOW PRESSURE SEAL (SEE KIT 70-0433 & 70-0434)	SEE KIT	3	49	BOLT / PISTON	46-1216	3
22	O-RING (SEE KIT 70-0434)	25-0015	3	50	OIL DIP STICK	46-0144	1
23	LOW PRESSURE SEAL RETAINER (SEE KIT 70-0434)	SEE KIT	3	51	CRANKCASE	46-1209	1
24	OIT SEAL (SEE KIT 70-0432)	26-0047	3	52	CRANKCASE COVER	46-1208	1
25	BUSHING	9-0029	3	53	O-RING	25-0060	1
26	O-RING	25-0052	1	54	OIL LEVEL INDICATOR	46-0574	1
27	BOLT	27-8431	4	55	SIGHTGLASS COVER	46-1207	1
28	OIL SEAL	26-0049	1	56	BOLT	27-8433	4

REPLACEMENT KITS


Mi-T-M KIT#	DESCRIPTION	ITEMS	# OF ASSEMBLIES	# OF CYLINDERS
70-0432	OIL SEAL KIT	24	3	3
70-0431	VALVE KIT	5	6	3
70-0433	LOW/HIGH PRESSURE SEALS	19, 21	3	3
70-0434	PACKING KIT	19-23	1	1

EX-9807-051614

8-0522-060513 MLK							
UNLOADER ASSEMBLY (8-0522)							
REF. #	DESCRIPTION	PART #	QTY.		REF. #	DESCRIPTION	PART # QTY.
1	Brass Cap	8-0534	1		14	Spacer	8-0539 1
2	Spring	49-0149	1		15	O-ring	25-0368 1
3	Spring Guide	8-0535	1		16	Shutter	8-0540 1
4	Ball	8-0318	1		17	Seat	8-0541 1
5	Back-up Ring (See 70-0342)	25-0529	1		18	O-ring	25-0220 2
6	O-ring (See 70-0342)	25-0530	1		19	Valve Body	8-0542 1
7	Piston	8-0536	1		20	Check Valve Seat	8-0543 1
8	Lock Ring	8-0537	1		21	O-ring	25-0369 1
9	Set Screw	8-0408	1		22	Check Valve	8-0486 1
10	Piston Housing	8-0538	1		23	Spring	49-0150 1
11	O-ring	25-0189	1		24	O-ring	25-0325 1
12	Back-up Ring (See 70-0343)	25-0531	1		25	Nipple	8-0485 1
13	O-ring (See 70-0343)	25-0532	1				

REPLACEMENT KITS			
Mi-T-M KIT#	DESCRIPTION	ITEMS	QTY
70-0342	KIT-UPPER SEAL	5, 6	1
70-0343	KIT-LOWER SEAL	12, 13	1

HONDA ENGINE ASSEMBLY (851-0385)



851-0385 053111

851-0385 053111			
ENGINE ASSEMBLY			
ITEM	DESCRIPTION	Mi-T-M #	QTY
1	DRAIN HOSE	70-0555	1
2	MUFFLER	45-0161	1
3	ENGINE	1-0184	1
4	HOSE CLIP	33-0517	1
5	BOLT	27-8898	1

