



## Lockset Function Selection Guide

Selecting the proper lockset function can be a confusing task, especially when faced with so many options. This guide has been designed to assist in proper selection based on desired function.

### Lock Functions– Based on ANSI A156.2

The following lock functions are explained based on the ANSI standard, which should be universal across several manufacturers. There may be several other functions available, but these are the most common, as found in many commercial and residential applications.



### Non-Keyed Functions

Single Dummy Trim- F170	Passage Latch– F75	Exit Lock	Bath/Bedroom Privacy- F76
Single dummy trim for one side of door. Used for door pull or as a matching inactive trim.	Both sides are always unlocked. Inside always free for immediate egress.	Blank plate outside, inside always unlocked and free for immediate egress.	Push button locking. Can be unlocked from outside with small screwdriver. Turn inside piece or close door to release button. Inside always free for immediate egress.
Outside or Inside	Outside Inside	Outside Inside	Outside Inside

### Keyed Functions

Entrance/Office Lock– F82	Entrance Lock– F109	Classroom Lock– F84	Storeroom Lock– F86
Push button locking, locks outside until it is unlocked with key or by rotating inside piece. Inside is always free for immediate egress.	Turn/Push button locks outside requiring the use of a key, until button is manually unlocked. Push button locks outside until opened with key or by rotating inside. Inside always free for immediate egress.	Outside is locked or unlocked by key. Inside is always unlocked and free for immediate egress.	Outside lever is fixed, entrance by key only. Inside lever is always unlocked and free for immediate egress.
Outside Inside	Outside Inside	Outside Inside	Outside Inside

Information sources include ANSI A156.2, Schlage, Arrow and Yale



If you are still having difficulty choosing a lockset, please contact us at [askzoro@zoro.com](mailto:askzoro@zoro.com) or 855-289-9676

Product Compliance and Suitability.

THE PRODUCT STATEMENTS CONTAINED IN THIS EZTIP ARE INTENDED FOR GENERAL INFORMATIONAL PURPOSES ONLY. SUCH PRODUCT STATEMENTS DO NOT CONSTITUTE A PRODUCT RECOMMENDATION OR REPRESENTATION AS TO THE APPROPRIATENESS, ACCURACY, COMPLETENESS, CORRECTNESS OR CURRENTNESS OF THE INFORMATION PROVIDED. INFORMATION PROVIDED IN THIS EZTIP DOES NOT REPLACE THE USE BY YOU OF ANY MANUFACTURER INSTRUCTIONS, TECHNICAL PRODUCT MANUAL OR OTHER PROFESSIONAL RESOURCE OR ADVISER AVAILABLE TO YOU. ALWAYS READ, UNDERSTAND, AND FOLLOW ALL MANUFACTURER INSTRUCTIONS.