

Replacement Elements

35 - 6600 SCFM Flow Range



Small Elements
with Molded Endcaps




Compact & Large Elements
with Metal Endcaps

Features

- Pleated media for high dirt holding capacity
- Polyester: Reinforced with epoxy coated steel wire on both sides of cloth
- Paper: Heavy duty industrial strength paper surrounded by heavy gauge galvanized expanded metal
- 40 - 50% increased dust loading capacity with prefilter (part number suffix P)
- Optimal surface area per given size

Technical Specifications

- Polyester: 99%+ removal efficiency to 5 micron
- Paper: 99%+ removal efficiency to 2 micron
- Temp (continuous): min -26°F (-15°C), max 220°F (104°C)
- Filter change out differential: 15-20" H₂O over initial ΔP



Polyester Media Benefits

- Washable with lukewarm water & mild detergent
- Less maintenance due to longer durability
- Moisture resistant
- Handles hot air and oil mist from unload cycle of reciprocating/ piston compressor

Paper Media Benefits

- Optimal surface area per given size
- Higher efficiency than many alternative media
- Cost effective

Replacement Elements—up to 300 SCFM flow

Element Part Number		Element SCFM Rating	Surface Area ft ²		Dimensions - inches			STD Endcap Features
Polyester	Paper		Polyester	Paper	ID	OD	HT	
15P	14P	35	0.50	1.12	3	4 3/8	2 5/16	M
19P	18P	100	1.50	3.00	3	4 3/8	4 3/4	M
31P	30P	195	2.30	6.20	3 5/8	5 3/4	4 3/4	M
35P	34P	275	4.00	11.00	4 3/4	7 7/8	4 13/16	M
231P	230P	300	4.50	11.8	3 5/8	5 3/4	9 1/2	M

Note: Also available in wire mesh. Example part number for wire mesh: 230S

Dimension tolerance $\pm 1/4"$

See Element Technical Data section for maintenance guidelines

Replacement Elements—up to 6600 SCFM flow

Element Part Number		Element SCFM Rating	Surface Area ft ²		Dimensions - inches			STD Endcap Features
Polyester	Paper		Polyester	Paper	ID	OD	HT	
235P	234P	570	8.3	22.8	4 3/4	7 7/8	9 5/8	M
335P	334P	800	12	34	4 3/4	7 7/8	14 1/2	M
237	236	550	8.6	22.6	4 2/3	7 3/4	8 1/2	GBN
239P	238P	570	11.5	52	4 7/8	9 1/4	10	GBN
245P	244P	880	14	35.5	6	9 3/4	9 5/8	GN M
345P	344P	1100	22.1	57	6	9 3/4	14 1/2	GN
275P	274P	1100	19	45.4	8	11 3/4	9 5/8	GN
375P	374P	1500	28	68.1	8	11 3/4	14 1/2	GN
377P	376P	1825	50	125	9	14 5/8	14 1/2	GN
385P	384P	3300	50	140	14	19 5/8	14 1/2	GN
485P	484P	4705	75	200	14	19 5/8	21 1/2	GN
685P	--	6600	100	--	14	19 5/8	28 1/2	GN

Note: Most are available in wire mesh. Example part number for wire mesh: 244S

Dimension tolerance $\pm 1/4"$

See Element Technical Data section for maintenance guidelines

Endcap Information

- M = Molded plastisol
- B = Closed one end with bolt hole, open on other end
- G = Galvanized metal endcaps
- N = Neoprene gaskets on open end(s)

Additional Media Options

- 1, 4, 25, and 100 micron Polyester
- HEPA
- Stainless steel wire mesh
- High temperature Nomex
- Stainless steel Nomex reinforced by stainless steel wire mesh & expanded metal
- Polypropylene
- Activated carbon